



20266084

**Thermostat w. change-over contact and centre plate, Q.x, alu velvety, lacq.**

**Technical characteristics**

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

**Electric current**

Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
"Switching current ""Cooling"" at $\cos \varphi = 0.6$ "	2 A
"Switching current ""Cooling"""	5 A

**Measurement**

Range of temperatures	5 / 30 °C
-----------------------	-----------

**Materials**

Colour of design line	aluminium
Material / workmanship	lacquered

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Type of connection	with plug-in terminals
--------------------	------------------------

**Equipment**

Switching temperature difference	≈ 0.5 K
Heating	for heating or cooling mode
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Energy efficiency class	I (1%)
-------------------------	--------

**temperatur**

Temperature	5...30 °C
-------------	-----------

**Identification**

---

Application, usage	HVAC control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

---