



20301404

Thermostat, NC contact, centre plate, rocker switch, B.7, al., matt, lacq.

Technical characteristics

Functions

Switching with on/off switch and indicator LED for "on"

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$	max. 4 A
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
Switching current	10 A

Dimensions

Insertion depth	24.5 mm
-----------------	---------

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Materials

Colour of design line	aluminium
Material / workmanship	lacquered

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

Equipment

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

Use

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Energy efficiency class	I (1%)
temperatur	
Temperature	5...30 °C
Identification	
Application, usage	HVAC control
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7