



20301606

**Thermostat, NC contact, centre plate, rocker switch, B.3/B.7, ant., matt**

**Technical characteristics**

**Functions**

Switching	with on/off switch and indicator LED for "on"
-----------	---

With cooling function	Yes
-----------------------	-----

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

**Electric current**

Inductive load at $\cos \varphi = 0.6$	max. 4 A
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
Switching current	10 A

**Dimensions**

Insertion depth	24.5 mm
-----------------	---------

**Measurement**

Range of temperatures	5 / 30 °C
-----------------------	-----------

**Materials**

Colour of design line	anthracite
-----------------------	------------

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

**Equipment**

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

**Use**

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Energy efficiency class	I (1%)
<b>temperatur</b>	
Temperature	5...30 °C
<b>Identification</b>	
Application, usage	HVAC control
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7