



20316089

Temp. cont., NCcontact, Cen. plate, 24V AC/DC, rocker switch,Q.1/Q.3, p.wh.velv.

Technical characteristics

Functions

Switching with on/off switch and indicator LED for "on"

Main electrical features

Nominal voltage	24 V
Rated voltage	24 V AC/DC
Frequency	50/60 Hz

Electric current

Switching current	10 A~/4 A=
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Materials

Colour of design line	polar white
-----------------------	-------------

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

Equipment

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

Use

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

temperatur

Temperature

5...30 °C

Identification

Application, usage

HVAC control

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9