



3315412045

VGA soc. out., screw-in lift terminals, R.1/R.3, black glossy

Technical characteristics

Connectivity

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

Frequency

Frequency range video	max. 160 MHz
-----------------------	--------------

Screen

Resolution	max. 1280 x 1024 px
------------	---------------------

Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	Plastic/metal
Material for printing	PC-PMA black

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Connection

Conductor cross-section	max. 1.5 mm ²
Type of connection	with screw-in lift terminals for connection to 15-core VGA cable

Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

Equipment

Type of configuration	Laserdruck
Supporting plate / Supporting ring	with supporting ring

Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Identification

Application, usage	Communication technology
Main design line	Berker R.1/R.3/R.8

Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74