



20441404

Thermostat, NO contact, centre plate, time-controlled, B.7, al., matt, lacq.

Technical characteristics

Functions

Function	timer for changing the temperature by the hour ; with valve protection function ; Operating hours meter or energy consumption display adjustable ; with access protection ; with frost protection function
Slide switch	with switchover manual/automatic mode

Controls and indicators

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

Electric current

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

Dimensions

Insertion depth	25 mm
-----------------	-------

Power

Power consumption	≈ 1.2 W
-------------------	---------

Battery

Lithium cell power reserve [years]	≈ 10
------------------------------------	------

Detection

Sensor	with integrated temperature sensor
--------	------------------------------------

Materials

Colour of design line	aluminium
Material / workmanship	lacquered

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with screw terminals
Connection	with additional connection for external floor temperature sensor/remote sensor

Settings

Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	programmable with operating unit removed ; 3 preset time programmes, individually adjustable ; max. 9 switching times per weekday ; 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun
Time	with automatic summer-/winter time switching (can be switched off)

Equipment

Switching temperature difference	≈ 0.5 K
Heating	with self-teaching heating curve ; for heating or cooling mode ; for room and floor heaters ; for underfloor heating control using room and/or floor temperature possible
Control	PWM cycle time and hysteresis (for two-point control) settable ; control process PWM or 2-point (on/off) can be selected
Valve drives	type of actuator (currentless closed/open) adjustable

Use

Differentiation characteristic 2 - Sales	Time-controlled
--	-----------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)

Identification

Application, usage	HVAC control
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7