



20446089

**Thermostat, NO contact, centre plate, time-controlled, Q.1, p. white velvety**

**Technical characteristics**

**Functions**

Function	with access protection, timer for changing the temperature by the hour, with frost protection function, with valve protection function, Operating hours meter or energy consumption display adjustable
Slide switch	with switchover manual/automatic mode
With cooling function	Yes

**Controls and indicators**

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

**Main electrical features**

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

**Electric current**

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

**Dimensions**

Insertion depth	25 mm
-----------------	-------

**Power**

Power consumption	≈ 1.2 W
-------------------	---------

**Battery**

Lithium cell power reserve [years]	≈ 10
------------------------------------	------

**Detection**

Sensor	with integrated temperature sensor
--------	------------------------------------

**Materials**

Colour of design line	polar white
Colour	polarwhite
Material	Plastic/metal

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Type of connection	with screw terminals
Connection	with additional connection for external floor temperature sensor/remote sensor
<b>Settings</b>	
Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	3 preset time programmes, individually adjustable, max. 9 switching times per weekday, programmable with operating unit removed, 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun
Time	with automatic summer-/winter time switching (can be switched off)
<b>Equipment</b>	
Switching temperature difference	≈ 0.5 K
Heating	for room and floor heaters, for underfloor heating control using room and/or floor temperature possible, for heating or cooling mode, with self-teaching heating curve
Control	control process PWM or 2-point (on/off) can be selected, PWM cycle time and hysteresis (for two-point control) settable
Valve drives	type of actuator (currentless closed/open) adjustable
<b>Use</b>	
Differentiation characteristic 2 - Sales	Time-controlled
<b>Use conditions</b>	
Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)
<b>Identification</b>	
Application, usage	HVAC control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9