



20446089

Thermostat, NO contact, centre plate, time-controlled, Q.1, p. white velvety

Technical characteristics

Functions

Function	with access protection ; timer for changing the temperature by the hour ; with frost protection function ; with valve protection function ; Operating hours meter or energy consumption display adjustable
Slide switch	with switchover manual/automatic mode
With cooling function	Yes

Controls and indicators

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

Electric current

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

Dimensions

Insertion depth	25 mm
-----------------	-------

Power

Power consumption	≈ 1.2 W
-------------------	-----------------

Battery

Lithium cell power reserve [years]	≈ 10
------------------------------------	--------------

Detection

Sensor	with integrated temperature sensor
--------	------------------------------------

Materials

Colour of design line	polar white
-----------------------	-------------

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Connection	with additional connection for external floor temperature sensor/remote sensor
Settings	
Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	3 preset time programmes, individually adjustable ; max. 9 switching times per weekday ; programmable with operating unit removed ; 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun
Time	with automatic summer-/winter time switching (can be switched off)
Equipment	
Switching temperature difference	≈ 0.5 K
Heating	for room and floor heaters ; for underfloor heating control using room and/or floor temperature possible ; for heating or cooling mode ; with self-teaching heating curve
Control	control process PWM or 2-point (on/off) can be selected ; PWM cycle time and hysteresis (for two- point control) settable
Valve drives	type of actuator (currentless closed/open) adjustable
Use	
Differentiation characteristic 2 - Sales	Time-controlled
Safety	
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)
Identification	
Application, usage	HVAC control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9