



20447104

Thermostat, NO contact, centre plate, time-controlled, K.5, stainl. steel, lacq.

Technical characteristics

Functions

Function	timer for changing the temperature by the hour, with access protection, with valve protection function, with frost protection function, Operating hours meter or energy consumption display adjustable
Slide switch	with switchover manual/automatic mode

Controls and indicators

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

Electric current

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

Dimensions

Insertion depth	25 mm
-----------------	-------

Power

Power consumption	≈ 1.2 W
-------------------	---------

Battery

Lithium cell power reserve [years]	≈ 10
------------------------------------	------

Detection

Sensor	with integrated temperature sensor
--------	------------------------------------

Materials

Colour of design line	stainless steel
Colour	stainless steel
Material / workmanship	lacquered
Material	Plastic/metal

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with screw terminals
Connection	with additional connection for external floor temperature sensor/remote sensor
Settings	
Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	3 preset time programmes, individually adjustable, 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun, max. 9 switching times per weekday, programmable with operating unit removed
Time	with automatic summer-/winter time switching (can be switched off)
Equipment	
Switching temperature difference	≈ 0.5 K
Heating	for heating or cooling mode, with self-teaching heating curve, for room and floor heaters, for underfloor heating control using room and/or floor temperature possible
Control	PWM cycle time and hysteresis (for two-point control) settable, control process PWM or 2-point (on/off) can be selected
Valve drives	type of actuator (currentless closed/open) adjustable
Use	
Differentiation characteristic 2 - Sales	Time-controlled
Use conditions	
Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)
Identification	
Application, usage	HVAC control
Main design line	Berker K.5