



383620

Change-over switch f. lock cylinders, earth contact, splash-prot. flush-mtd IP44

Technical characteristics

Architecture

Type of control unit	Key
----------------------	-----

Configuration

Switch mode	Off/change-over
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	16 AX (200 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	40.2 mm
Height	71 mm
Width	71 mm

Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Closures / Key systems	for master-key systems
Lock cylinder	for lock cylinder
Heating switch	No

Use cases

Application	Blind control ; Light control
-------------	-------------------------------

Use	
Differentiation characteristic 2 - Sales	with earth contact
Safety	
Protection index IP	IP44
Identification	
Application, usage	Light control
Main design line	Splash-protected flush-mounted IP44
Instructions	
Information text	for standardised profile half-cylinder lock, 40 mm