



41092089

**SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,R.classic,wh**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Power**

Power consumption	0.25 W/0.35 VA
-------------------	----------------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Detection**

Sensor	integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness
--------	---

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white

**Lighting control**

Switch-off brightness	≈ 4 lx
Switch-on brightness	≈ 2 lx
Light intensity (white)	0.2 cd

**LED control**

LED	white LED light, long service life of the LED
-----	---

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Conductor cross-section (rigid)	2.5
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

**Cable**

Wiring	through-wiring possible, therefore also ideal for retrofitting
--------	--

**Settings**

Shading parameter	R1_biały
Laser parameter	R1_weiß

**Equipment**

Type of configuration	Laserdruck
Lighting	additional benefit by combination of a socket outlet with an orientation light

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

**Safety**

Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

Main design line	Serie 1930/R.classic
Secondary design line(s)	Serie 1930, Series R.classic

**Instructions**

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--

Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.
------------------	--