



28199949

Rot. dimmer cover plate, setting knob, S.1, ant., matt

Technical characteristics

Architecture

Type of control unit Rotative

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fuse short-circuit and overload proof (fine-wire fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Loss power at full load ≈ 4 W

Materials

Colour of design line anthracite

Colour anthracite

Material thermoplastic

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 60...400 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load Resistive load

Type of connection with screw terminals

Equipment

Dimming principle phase cut-on

Switches / socket outlets with rotary on/off switch

Use

Differentiation characteristic 2 - Sales	Setting knob
Differentiation characteristic 3 - Sales	with soft-lock

Use conditions

Operating temperature	5...25 °C
-----------------------	-----------

Identification

Application, usage	Light control
Main design line	Berker S.1
Secondary design line(s)	House electronics