



2874

## Tronic rotary dimmer with soft-lock, house electronics

### Technical characteristics

#### Architecture

Type of control unit Push & rotative

#### Functions

Soft startup bulb-preserving soft startup

#### Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

#### Voltage

Operating voltage 230 V AC

Voltage voltage test possible without dismantling

#### Fuse

Fuse short-circuit and overload proof (electronic fuse)

#### Dimensions

Axis dimension Ø 4 mm

#### Power

Loss power at full load ≈ 5 W

Electronic transformers 20...525 W

#### Materials

Colour not applicable

Material Plastic/metal

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps 20...525 W

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Type of load capacitive

Terminal with terminal for base load from mains isolator

Type of connection with plug-in terminals

#### Equipment

Dimming principle phase cut-off

low noise	very low noise
Switches / socket outlets	with change-over pressure switch
<b>Use</b>	
Differentiation characteristic 3 - Sales	with soft-lock
<b>Identification</b>	
Application, usage	Light control
Release issue	2
Main design line	Light control
<b>Instructions</b>	
Information text	Trouble-free operation will be obtained only with Berker Tronic® transformers.