



2875

## Rotary dimmer with soft-lock house electronics

### Technical characteristics

#### Architecture

Type of control unit Push & rotative

#### Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

#### Voltage

Operating voltage 230 V AC

Voltage voltage test possible without dismantling

#### Fuse

Fuse with spare fuse ; short-circuit and overload proof (fine-wire fuse)

#### Dimensions

Axis dimension  $\varnothing$  4 mm

#### Power

Loss power at full load  $\approx$  6 W

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps 60...600 W

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Type of load Resistive load

Type of connection with plug-in terminals

#### Equipment

Dimming principle phase cut-on

Switches / socket outlets with change-over pressure switch

#### Use

Differentiation characteristic 3 - Sales with soft-lock

#### Identification

Application, usage Light control

Main design line Light control

**Instructions**

---

Information text

Possible to change fuse without removing cover.