



2875

Rotary dimmer with soft-lock house electronics

Technical characteristics

Architecture

Type of control unit Push & rotative

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Voltage voltage test possible without dismantling

Fuse

Fuse with spare fuse ; short-circuit and overload proof (fine-wire fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Loss power at full load ≈ 6 W

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 60...600 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load Resistive load

Type of connection with plug-in terminals

Equipment

Dimming principle phase cut-on

Switches / socket outlets with change-over pressure switch

Use

Differentiation characteristic 3 - Sales with soft-lock

Identification

Application, usage Light control

Main design line Light control

Instructions

Information text

Possible to change fuse without removing cover.