



2875

Rotary dimmer with soft-lock house electronics

Technical characteristics

Architecture

Type of control unit	Push & rotative
----------------------	-----------------

Main electrical features

Nominal voltage	230 V
Frequency	50 Hz

Voltage

Operating voltage	230 V AC
Voltage	voltage test possible without dismantling

Fuse

Fuse	with spare fuse, short-circuit and overload proof (fine-wire fuse)
------	--

Dimensions

Axis dimension Ø	4 mm
------------------	------

Power

Loss power at full load	≈ 6 W
-------------------------	-------

Materials

Colour	not applicable
Material	Plastic/metal

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	60...600 W
--	------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of load	Resistive load
Type of connection	with plug-in terminals

Equipment

Dimming principle	phase cut-on
Switches / socket outlets	with change-over pressure switch

Use

Differentiation characteristic 3 - Sales	with soft-lock
--	----------------

Identification	
Application, usage	Light control
Main design line	Light control
Instructions	
Information text	Possible to change fuse without removing cover.