



41101913

SCHUKO soc.out. LED+"SV" impr.,labfield,enhncd contact prot., S1/B3/7een

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Design lines special colours	green
Colour	green
Colour	green
RAL colour	RAL 6029 - Mint green
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 2 - Sales

enhanced contact protection

Differentiation characteristic 3 - Sales

Screw-in lift terminals

Standards

Execution SV, ZSV

according to VDE 0100-710

Safety

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

Identification

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Information text

Labelling field height arranged for P-touch strips 6 mm. ; Insert colour-coded.