



2885

Rotary dimmer with soft-lock house electronics

Technical characteristics

Architecture

Type of control unit Push & rotative

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Loss power at full load ≈ 5 W

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 100...1000 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of load Resistive load

Type of connection with screw terminals

Equipment

Dimming principle phase cut-off

Switches / socket outlets with change-over pressure switch

Use

Differentiation characteristic 3 - Sales with soft-lock

Identification

Application, usage Light control

Main design line Light control