



2885

## Rotary dimmer with soft-lock house electronics

### Technical characteristics

#### Architecture

Type of control unit Push & rotative

#### Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

#### Voltage

Operating voltage 230 V AC

#### Fuse

Fuse short-circuit and overload proof (electronic fuse)

#### Dimensions

Axis dimension Ø 4 mm

#### Power

Loss power at full load ≈ 5 W

#### Materials

Colour not applicable

Material Plastic/metal

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps 100...1000 W

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Type of load Resistive load

Type of connection with screw terminals

#### Equipment

Dimming principle phase cut-off

Switches / socket outlets with change-over pressure switch

#### Use

Differentiation characteristic 3 - Sales with soft-lock

#### Identification

Application, usage Light control

