



289110

1-10 V rot. potentiometer, soft-lock, light control

Technical characteristics

Architecture

Type of control unit Push & rotative

Functions

Switching for switching and controlling electronic ballasts and 10 V Tronic transformers, 105 W

Connectivity

Interface according to DIN EN 61347-2-3

Main electrical features

Nominal voltage 230 V

Frequency 50/60 Hz

Electric current

Control current 50 mA

Switching current 6 A

Fuse

Fuse short-circuit and overload proof (fine-wire fuse) ; with spare fuse

Dimensions

Axis dimension \varnothing 4 mm

Connection

Type of connection with screw terminals

Settings

Setting basic brightness programmable

Equipment

Lighting e.g. for fluorescent lamps and LV halogen lamps

Switches / socket outlets with on/off pressure switch

Use

Differentiation characteristic 3 - Sales Soft-lock

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Identification

Application, usage

Light control

Main design line

Light control

Instructions

Information text

To ensure same illumination, use only electronic ballasts and fluorescent lamps from the same manufacturers. Possible to change fuse without removing cover.