



41106013

SCHUKO soc.out. LED+"SV" impr.,labfield,enhncd contact prot.,screw-in lift ,Q.x

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Design lines special colours	green
Colour	green
Colour	green
RAL colour	RAL 6029 - Mint green
Material	duroplastic
Surface appearance	velvety

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 2 - Sales	enhanced contact protection

Standards

Execution SV, ZSV

according to VDE 0100-710

Safety

Protection index IP

IP20

REACH conform

Yes

RoHS conform

Yes

Halogen free

No

Protection

Enhanced contact protection

With enhanced contact protection

Yes

Identification

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text

Labelling field height arranged for P-touch strips 6 mm. ; Insert colour-coded.