



289610

## 1-10 V push-button rot. potentiometer, NO contact, soft-lock, light control

### Technical characteristics

#### Architecture

Type of control unit Push & rotative

#### Controls and indicators

Control for activation of pulse relays

#### Connectivity

Interface according to DIN EN 61347-2-3

Interface for controlling electronic ballasts and Tronic transformers with 1 - 10 V interface, 105 W

#### Main electrical features

Nominal voltage 240 V

Frequency 50/60 Hz

#### Electric current

Control current 50 mA

Momentary-contact current max. 2 A

#### Fuse

Fuse short-circuit and overload proof (fine-wire fuse) ; with spare fuse

#### Dimensions

Axis dimension Ø 4 mm

#### Connection

Type of connection with screw terminals

#### Equipment

Lighting e.g. for fluorescent lamps and LV halogen lamps

Switches / socket outlets with push-button, NO contact

#### Use

Differentiation characteristic 3 - Sales Soft-lock

#### Safety

REACH conform Yes

RoHS conform Yes

#### Identification

Application, usage Light control

Main design line Light control

**Instructions**

---

Information text

To ensure same illumination, use only electronic ballasts and fluorescent lamps from the same manufacturers. Possible to change fuse without removing cover.