



29517003

LED signal light, RGB, K.5, al., matt, lacq.

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Rated voltage	230 V AC
---------------	----------

Frequency	50/60 Hz
-----------	----------

Power

Power consumption	at 195 ... 265 V~, 50/60 Hz - max. 2 W
-------------------	--

Materials

Colour	aluminium
--------	-----------

Colour	aluminium optics
--------	------------------

RAL colour	RAL 9006 - White aluminium
------------	----------------------------

Material / workmanship	lacquered
------------------------	-----------

Material	Plastic/metal
----------	---------------

Surface appearance	matt
--------------------	------

LED control

Quantity LED lamps	4
--------------------	---

Installation, mounting

For installation in standard wall boxes	according to DIN 49073-1
---	--------------------------

Connection

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Settings

Setting	Brightness modifiable via potentiometer
---------	---

Equipment

Lighting	Colour sequence can be stopped at any position via the push-button., Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button
----------	--

Switches / socket outlets	colour is switchable via an external switch
---------------------------	---

Use cases

Application	Light control
-------------	---------------

temperatur

Ambient temperature	-5...40 °C
---------------------	------------

Identification	
Main design line	Berker K.5
Instructions	
Special note text	For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length.