



41108913

**SCHUKO soc.out. LED+"SV" impr.,labfield,enhncd contact prot., S1/B3/7een**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

**Cover, door**

Cover Central cover plate

**Materials**

Design lines special colours green

Surface appearance glossy

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

**Use**

Differentiation characteristic 1 - Sales with labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

**Standards**

Execution SV, ZSV according to VDE 0100-710

**Safety**

---

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | IK02                        |
| REACH conform                                 | Yes                         |
| RoHS conform                                  | Yes                         |
| Halogen free                                  | No                          |
| Protection                                    | Enhanced contact protection |
| With enhanced contact protection              | Yes                         |

---

**Identification**

---

|                          |                                      |
|--------------------------|--------------------------------------|
| Main design line         | Berker S.1/B.3/B.7                   |
| Secondary design line(s) | Berker S.1 ; Berker B.3 ; Berker B.7 |

---

**Instructions**

---

|                  |   |
|------------------|---|
| Information text | Labelling field height arranged for P-touch strips 6 mm. ; Insert colour-coded. |
|------------------|---|

---