



29517009

LED signal light, RGB, K.1, p. white glossy

Technical characteristics

Main electrical features

| | |
|---------------|----------|
| Rated voltage | 230 V AC |
| Frequency | 50/60 Hz |

Power

| | |
|-------------------|--|
| Power consumption | at 195 ... 265 V~, 50/60 Hz - max. 2 W |
|-------------------|--|

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Surface appearance | glossy |

LED control

| | |
|--------------------|---|
| Quantity LED lamps | 4 |
|--------------------|---|

Installation, mounting

| | |
|---|--------------------------|
| For installation in standard wall boxes | according to DIN 49073-1 |
|---|--------------------------|

Connection

| | |
|-------------------------|---------------------|
| Conductor cross-section | 2.5 mm ² |
|-------------------------|---------------------|

Settings

| | |
|---------|---|
| Setting | Brightness modifiable via potentiometer |
|---------|---|

Equipment

| | |
|---------------------------|---|
| Lighting | Colour sequence can be stopped at any position via the push-button. ; Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button |
| Switches / socket outlets | colour is switchable via an external switch |

Use cases

| | |
|-------------|---------------|
| Application | Light control |
|-------------|---------------|

temperatur

| | |
|---------------------|------------|
| Ambient temperature | -5...40 °C |
|---------------------|------------|

Identification

| | |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

Instructions

| | |
|-------------------|--|
| Special note text | For consistent illumination of all pilot lamps, connect max. 5 devices per 10 m of cable length. |
|-------------------|--|

