



29537004

LED signal light, white lighting, K.5, stainless steel matt, lacq.

Technical characteristics

Main electrical features

| | |
|---------------|----------|
| Rated voltage | 230 V AC |
| Frequency | 50/60 Hz |

Power

| | |
|-------------------|-----------------------------|
| Power consumption | at 230 V~, 50 Hz - max. 1 W |
|-------------------|-----------------------------|

Materials

| | |
|------------------------|-----------------|
| Colour of design line | stainless steel |
| Material / workmanship | lacquered |
| Surface appearance | matt |

LED control

| | |
|--------------------|---|
| Quantity LED lamps | 4 |
|--------------------|---|

Installation, mounting

| | |
|---|--------------------------|
| For installation in standard wall boxes | according to DIN 49073-1 |
|---|--------------------------|

Connection

| | |
|-------------------------|---------------------|
| Conductor cross-section | 2.5 mm ² |
|-------------------------|---------------------|

Settings

| | |
|---------|---|
| Setting | Brightness modifiable via potentiometer |
|---------|---|

Equipment

| | |
|---------------------------|--------------------------------|
| Lighting | Light colour cold white |
| Switches / socket outlets | switchable via separate switch |

Use cases

| | |
|-------------|---------------|
| Application | Light control |
|-------------|---------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

temperatur

| | |
|---------------------|------------|
| Ambient temperature | -5...40 °C |
|---------------------|------------|

Identification

| | |
|------------------|------------|
| Main design line | Berker K.5 |
|------------------|------------|