



41231404

**SCHUKO soc.out., enhanced contact prot., screw-in lift term., B.7, al. matt lacq.**

#### Technical characteristics

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Electric current

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

##### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

##### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7