



303550

Series switch for hollow-wall mounting, module inserts

Technical characteristics

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode series

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Height 71 mm

Width 71 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode without spreader claws ; low installation depth ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

| | |
|-----------------------|-------------------------------------|
| Lighting | for lighting and monitoring circuit |
| Heating switch | No |
| Use cases | |
| Application | Light control |
| Safety | |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Identification | |
| Application, usage | Light control |
| Main design line | Light control |