



3036

Change-over switch 10AX 250V~, Light control

Technical characteristics

Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

Functions

Switching angle	3.5 °
-----------------	-------

Configuration

Switch mode	Off/change-over
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	41.6 mm
Insertion depth	31 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws, for screw fastening
-------------------	--

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1

Type of connection	with plug-in terminals
Type of connection	Quickconnect
Equipment	
Lighting	for lighting and monitoring circuit
Heating switch	No
Use cases	
Application	Barrier-free application, HVAC-control, Light control
Safety	
Protection index IP	IP20
Impact strength	IK07
Identification	
Application, usage	HVAC control, Light control
Appliance switch type	No
Main design line	Light control
Instructions	
Special note text	A control change-over switch is shown here as an example. With 2-pole and 3-pole control on/off switches, other rocker switches and neon lamp units are required.
Information text	spreader claws, insulated to the supporting ring, self-resetting