



3037

Intermediate switch, light control

Technical characteristics

Architecture

Type of control unit single rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode intermediate

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 42 mm

Insertion depth 32 mm

Height 71 mm

Width 71 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting	for lighting and monitoring circuit
Heating switch	No

Use cases

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Identification

Application, usage	HVAC control ; Light control
Appliance switch type	No
Main design line	Light control

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--
