



3315402045

**VGA soc. out., R.1/R.3, black glossy**

**Technical characteristics**

**Connectivity**

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

**Dimensions**

Insertion depth	12 mm
-----------------	-------

**Frequency**

Frequency range video	max. 160 MHz
-----------------------	--------------

**Screen**

Resolution	max. 1280 x 1024 px
------------	---------------------

**Materials**

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	Plastic/metal
Material for printing	PC-PMA black

**Installation, mounting**

Installation mode	without spreader claws, for screw fastening
-------------------	---

**Connection**

Type of connection	with backside jack for connecting to pre-assembled VGA cable
Connection	with 15pole D-subminiature double jack

**Settings**

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

**Equipment**

Type of configuration	Laserdruck
Supporting plate / Supporting ring	with supporting ring

**Identification**

Application, usage	Communication technology
Main design line	Berker R.1/R.3/R.8

**Instructions**

---

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74