



41436089

## SCHUKO soc. out., screw-in lift terminals, Q.x, p. white velvety

### Technical characteristics

#### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

#### Electric current

Rated current	16 A
---------------	------

#### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

#### Cover, door

Cover	Central cover plate
-------	---------------------

#### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	duroplastic
Surface appearance	velvety
Metallic colour	No

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

#### Use

**Safety**

---

IK protection code against mechanical impacts	02
Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No

---

**Identification**

---

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

---