



3315416084

**VGA socket outlet with screw-in lift terminals, Q.x, alu velvety, lacquered**

**Technical characteristics**

**Connectivity**

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

**Frequency**

Frequency range video	max. 160 MHz
-----------------------	--------------

**Screen**

Resolution	max. 1280 x 1024 px
------------	---------------------

**Materials**

Colour of design line	aluminium
Surface appearance	velvety

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Conductor cross-section	max. 1.5 mm <sup>2</sup>
Type of connection	with screw-in lift terminals for connection to 15-core VGA cable

**Equipment**

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

**Use**

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Identification**

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

**Instructions**

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74