



4582

WLAN Access-Point UP, com-tech

Technical characteristics

Functions

Operating mode Operating modes in WLAN: Access-Point, Repeater/Bridge, Client (WDS), Client (relayed)

Connectivity

Ethernet data rate 10/100 Mbit/s

Encoding Ciphering method: WEP, WPA, WPA2

Radio WLAN range can be configured for adaptation to spatial conditions

WLAN Standards IEEE 802.11 b/g/n

Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

Dimensions

Insertion depth 40 mm

Frequency

Frequency band 2.4 GHz

Power

Power consumption (operation) max. 3 W

Storage

Transfer rate WLAN max. 150 Mbit/s

Installation, mounting

For fitting in standard connection boxes according to DIN 49073 and DIN EN 60670

Connection

Type of connection with 2pole plug-in terminal for mains voltage

Connection with RJ45 jack on front ; LAN connection via 5pole screw terminal block

Scope of delivery

Component with integral WLAN antenna

Software

Update software updates available by download

Software Configuration of the integrated web server via web browser

Safety

Subject to technical modifications

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	Communication technology
Main design line	Communication technology
