



383620

Change-over switch f. lock cylinders, earth contact, splash-prot. flush-mtd IP44

Technical characteristics

Architecture

Type of control unit Key

Configuration

Switch mode Off/change-over

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 16 AX (200 W Self Ballasted Lamp (SBL))

Dimensions

Depth 40.2 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Closures / Key systems for master-key systems

Lock cylinder for lock cylinder

Heating switch No

Use cases

Application Blind control ; Light control

Use

Differentiation characteristic 2 - Sales

with earth contact

Safety

Protection index IP

IP44

Identification

Application, usage

Light control

Main design line

Splash-protected flush-mounted IP44

Instructions

Information text

for standardised profile half-cylinder lock, 40 mm