



459410

## Aerial soc. 4hole single box, DC-permeable, 1930/glass/R.classic

### Technical characteristics

#### Functions

Function	Suitable for HDTV
----------	-------------------

#### Connectivity

Connectors / jacks	remote supply via F-sockets
--------------------	-----------------------------

Outputs	with 2 independent SAT outputs (F-sleeves) and 2 IEC outputs (male/female)
---------	--

Reception / transmission	for terrestrial reception, for digital and analogue transmission
--------------------------	--

#### Voltage

Voltage	DC voltage conducting
---------	-----------------------

#### Frequency

Broadband technology	5...2400 MHz
----------------------	--------------

#### Resistance

Wave impedance	75 $\Omega$
----------------	-------------

#### Attenuation

Tap loss at 2150 MHz	2 dB
----------------------	------

Tap loss at 860 MHz	2 dB
---------------------	------

#### Materials

Material	metal
----------	-------

#### Installation, mounting

System	for community and broadband cable systems, for single and distributor SAT systems, for multi-switch systems
--------	---

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

Connection	for simultaneous connection of radio and TV receiver as well as 2 independent SAT receivers
------------	---

#### Settings

Programs	also to add SAT programmes in broadband cable systems
----------	---

#### Equipment

Supporting plate / Supporting ring	external eyelets on the supporting ring can be broken off for round designs
------------------------------------	---

#### Use

**Standards**

General standards

EN 50083-2 and EN 60728-4

**Safety**

Protective screen	(VHF/UHF) according to EN 50083-2, Class B, (SAT) according to EN 50083-2, Class A
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-25...55 °C
-----------------------	-------------

**Identification**

Application, usage	Communication technology
Main design line	Communication technology