



385620

Key push-button for profile half cylinders splash-protected flush-mounted IP44

Technical characteristics

Architecture

Type of control unit Key

Configuration

Switch mode change-over contact, usable as NC or NO

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 42 mm

Insertion depth 31.3 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Closures / Key systems for master-key systems

Use cases

Application Blind control ; Light control

Use

Differentiation characteristic 2 - Sales with earth contact

Safety

Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes

Identification

Application, usage	Light control
Main design line	Splash-protected flush-mounted IP44

Instructions

Information text	for standardised profile half-cylinder lock, 40 mm
------------------	--