



47086084

SCHUKO sock.outl. w. residual current circuit-breaker a. cont.prot., Q.x alu

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting
Type	type A for alternating currents and pulsating direct currents

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Measurement error current	30 mA
Rated current	16 A
Surge current resistance	250 A (8/20) μ s
Short-circuit resistance (with back-up fuse 20 AgL)	3 kA

Dimensions

Insertion depth	31.9 mm
-----------------	---------

Tripping

Trigger time	30 ms
--------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	Plastic/metal
Surface appearance	velvety

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use cases

Application	Security and safety systems
-------------	-----------------------------

Use

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

Standards

Tested	conform VDE 0664 (EN 61008)
--------	-----------------------------

Safety

IK protection code against mechanical impacts	02
Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9