



41092089

SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,R.classic,wh

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Power

Power consumption	0.25 W/0.35 VA
-------------------	----------------

Cover, door

Cover	Central cover plate
-------	---------------------

Detection

Sensor	integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness
--------	---

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white

Lighting control

Switch-off brightness	≈ 4 lx
Switch-on brightness	≈ 2 lx
Light intensity (white)	0.2 cd

<b>LED control</b>	
LED	white LED light, long service life of the LED
<b>Installation, mounting</b>	
Installation mode	with spreader claws
<b>Connection</b>	
Conductor cross-section (rigid)	2.5
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals
<b>Cable</b>	
Wiring	through-wiring possible, therefore also ideal for retrofitting
<b>Settings</b>	
Shading parameter	R1_biały
Laser parameter	R1_weiß
<b>Equipment</b>	
Type of configuration	Laserdruck
Lighting	additional benefit by combination of a socket outlet with an orientation light
<b>Use</b>	
Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Serie 1930/R.classic
Secondary design line(s)	Serie 1930, Series R.classic
<b>Instructions</b>	
Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.