



41096089

SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,Q.x,wh velv

## Technical characteristics

### Architecture

Design according to DIN 49440

### Configuration

Number of modules 1

### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

### Electric current

Rated current 16 A

### Dimensions

Insertion depth 32 mm

### Power

Power consumption 0.25 W/0.35 VA

### Cover, door

Cover Central cover plate

### Detection

Sensor integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness

### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

### Lighting control

Switch-off brightness  $\approx 4$  lx

Switch-on brightness  $\approx 2$  lx

Light intensity (white) 0.2 cd

### LED control

LED white LED light ; long service life of the LED

Installation, mounting		
Installation mode	with spreader claws	
Connection		
Conductor cross-section (rigid)	max. 2.5 mm²	
Connection terminals	according to IEC 60884-1	
Connection terminals	according to VDE 0620-1	
Type of connection	with screw-in lift terminals	
Cable		
Wiring	through-wiring possible, therefore also ideal for retrofitting	
Equipment		
Lighting	additional benefit by combination of a socket outlet with an orientation light	
Use		
Differentiation characteristic 2 - Sales	enhanced contact protection	
Differentiation characteristic 3 - Sales	Screw-in lift terminals	
Safety		
IK protection code against mechanical impacts	05	
REACH conform	No	
RoHS conform	Yes	
Protection	Enhanced contact protection	
With enhanced contact protection	Yes	
Identification		
Main design line	Berker Q.1/Q.3/Q.7/Q.9	
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9	
Instructions		
Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.	