



47413515

SCHUKO soc.out. hinged cover surface-mtd, W.1, grey matt, plastic

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	surface-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Labelling field (W x H)	50 x 16 mm
Height	76 mm
Width	76 mm

Cover, door

Hinged covers	with hinged cover that falls back, manual clip-in
---------------	---

Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Cable

Wire

with one entry for 2 cables and one entry for cable and tube

Equipment

Sealing

with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Use

Differentiation characteristic 1 - Sales

with labelling field

Safety

IK protection code against mechanical impacts

05

Protection index IP

IP55

REACH conform

Yes

RoHS conform

Yes

Protection

without enhanced contact protection

With enhanced contact protection

No

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Identification

Application, usage

Surface-mounted wet-room installation

Main design line

Berker W.1

Instructions

Information text

Labelling field height arranged for P-touch strips 12 mm. ; Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK