



47512089

SCHUKO soc. out. hinged cover, enhncd contact prot., R.1/R.3, p. white glossy

Technical characteristics

Architecture

| | |
|-------------|------------------------|
| Design | according to DIN 49440 |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Cover, door

| | |
|---------------|-----------------------------------|
| Hinged covers | with hinged cover that falls back |
| Cover | Central cover plate |

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| Colour | polarwhite |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | thermoplastic |
| Material for printing | ASA polar white |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1 |
| Type of connection | with plug-in terminals |

Settings

| | |
|-------------------|----------|
| Shading parameter | R1_biały |
| Laser parameter | R1_weiß |

Equipment

Use

| | |
|--|-----------------------------|
| Differentiation characteristic 2 - Sales | enhanced contact protection |
|--|-----------------------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

| | |
|------------|-----------------------------|
| Protection | Enhanced contact protection |
|------------|-----------------------------|

| | |
|----------------------------------|-----|
| With enhanced contact protection | Yes |
|----------------------------------|-----|

Identification

| | |
|--------------------|-------------------------------------|
| Application, usage | Flush-mounted wet-room installation |
|--------------------|-------------------------------------|

| | |
|------------------|--------------------|
| Main design line | Berker R.1/R.3/R.8 |
|------------------|--------------------|

| | |
|--------------------------|------------------------------------|
| Secondary design line(s) | Berker R.1, Berker R.3, Berker R.8 |
|--------------------------|------------------------------------|

Instructions

| | |
|-------------------|---|
| Special note text | these marked articles (see symbol) are only suitable for the water-protected flush-mounted installation IP44 in conjunction with the corresponding seal, frame and contact protection box (imprint "IP44"). |
|-------------------|---|