



41431909

**SCHUKO soc. out., screw-in lift terminals, S.1/B.3/B.7, p. white, matt, plastic**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance matt

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

**Use**

Differentiation characteristic 3 - Sales with screw-in lift terminals

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection

---

**Identification**

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7