



47526059

**SCHUKO soc.out. hinged cover+"EDV" impr. in red,enhncd contact prot.,Q.x, pw**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Hinged covers with self-closing hinged covers

Cover Central cover plate

**Materials**

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales Labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

|   |  |
|---|--|
| IK protection code against mechanical impacts | 02                                     |
| Protection index IP                           | IP44                                   |
| REACH conform                                 | Yes                                    |
| RoHS conform                                  | Yes                                    |
| Halogen free                                  | No                                     |
| Protection                                    | enhanced contact protection VDE 0620-1 |
| With enhanced contact protection              | Yes                                    |

**Identification**

|                          |   |
|--------------------------|---|
| Application, usage       | Flush-mounted wet-room installation               |
| Main design line         | Berker Q.1/Q.3/Q.7/Q.9                            |
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |

**Instructions**

|                   |   |
|-------------------|---|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with the corresponding sealing set. |
| Information text  | Labelling field height arranged for P-touch strips 6 mm.  |