



47526089

SCHUKO soc. out. hinged cover, enhncd contact prot., Q.x, p. white velvety

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Hinged covers with self-closing hinged covers

Cover Central cover plate

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales Labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

IK protection code against mechanical impacts	02
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
Information text	Labelling field height arranged for P-touch strips 6 mm.