



47633502

**SCHUKO soc.out. hinged cover surf.-mtd, enhncd contact prot.,W.1,p.white m.plas.**

#### Technical characteristics

##### Architecture

Design according to DIN 49440

##### Configuration

Hollow base ample room for wiring under the bases of the inserts

##### Main electrical features

Rated voltage 250 V AC

Rated current 16 A

##### Cover, door

Hinged covers with hinged cover that falls back, manual clip-in

Cover Complete housing

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Terminal with Wago clip-in 2-wire connection terminal for wiring ; with two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection with plug-in terminals

##### Cable

Wire with one entry for 2 cables and one entry for cable and tube

##### Equipment

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

##### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

##### Safety

Protection index IP IP55

REACH conform Yes

RoHS conform Yes

Halogen free Yes

With enhanced contact protection Yes

##### Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

---

**Identification**

---

Application, usage	Surface-mounted wet-room installation
--------------------	---------------------------------------

---

Main design line	Berker W.1
------------------	------------

---

**Instructions**

---

Information text	Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK
------------------	--