



47693502

WATERPROOF - COMPLETE PRODUCT - SCHUKO SOCKET WITH CP WITH FPL AND KEY

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	surface-mounting

Configuration

Hollow base	ample room for wiring under the bases of the inserts
Number of modules	1

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	0 mm
Height	76 mm
Width	76 mm

Cover, door

Hinged covers	with hinged cover that falls back, manual clip-in
---------------	---

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Connection

Conductor cross-section	1...2.5 mm ²
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Cable

Wire	with one entry for 2 cables and one entry for cable and tube
------	--

Equipment

Sealing	with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
---------	---

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	enhanced contact protection

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
Key	with 2 keys
With enhanced contact protection	No

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Surface-mounted wet-room installation
Main design line	Berker W.1

Instructions

Information text	Labelling field height arranged for P-touch strips 12 mm. ; Spare keys and other closures (max. 24) on request. ; Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK
------------------	--