



47893505

**SCHUKO soc.out.hinged cover surf.-mtd,identical lockings,enhncd contact prot.,W1**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	surface-mounting

**Configuration**

Hollow base	ample room for wiring under the bases of the inserts
Number of modules	1

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	0 mm
Height	76 mm
Width	76 mm

**Cover, door**

Hinged covers	with hinged cover that falls back, manual clip-in
---------------	---

**Materials**

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

**Connection**

Conductor cross-section	1...2.5 mm <sup>2</sup>
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Cable**

Wire	with one entry for 2 cables and one entry for cable and tube
------	--

**Equipment**

---

Sealing	with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
---------	---

**Use**

---

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	enhanced contact protection

**Safety**

---

IK protection code against mechanical impacts	05
Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Protection	Enhanced contact protection
Key	with 2 keys
With enhanced contact protection	No

**Use conditions**

---

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

**Identification**

---

Application, usage	Surface-mounted wet-room installation
Main design line	Berker W.1

**Instructions**

---

Information text	Labelling field height arranged for P-touch strips 12 mm. ; Spare keys and other closures (max. 24) on request. ; Hinged cover springs made of stainless steel, pins of quick-release lock made of ZAMAK
------------------	--