



503101

Push-button NO contact with two signal contacts

Technical characteristics

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode NO, with 2 separate signalling contacts

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Conductor cross-section (rigid) max. 2.5 mm²

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts 0

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

Use cases

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Identification

Application, usage	Light control
Main design line	Light control

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--