



503150

**Push-button, NO contact for installation in hollow walls, Module inserts**

**Technical characteristics**

**Architecture**

Type of control unit rocker

**Functions**

Switching angle 3.5 °

**Configuration**

Switch mode Normally open contact

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 10 A

**Dimensions**

Depth 41.6 mm

Insertion depth 19.5 mm

Height 71 mm

Width 71 mm

**Materials**

Material Plastic/metal

**Installation, mounting**

Installation mode low installation depth, without spreader claws, for screw fastening

**Connection**

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

**Scope of delivery**

With lamp No

**Equipment**

Quantity of NC contacts	0
Quantity of NO contacts	1
Lighting	for lighting and monitoring circuit
<b>Use cases</b>	
Application	Barrier-free application, HVAC-control, Light control
<b>Safety</b>	
Protection index IP	IP20
<b>Identification</b>	
Application, usage	HVAC control, Light control
Main design line	Light control